

Gas Permeable (GP) Solutions

Daily Cleaners

Manufacturer	Name	Lenses Approved
Alcon Vision LLC	Opti-Free Daily Cleaner	silicone/acryl and fluorosilicone/acryl copolymers
Bausch + Lomb	Boston Cleaner	silicone/acryl copolymers and fluoro-silicone acrylate lenses
Bausch + Lomb	Boston Advance Cleaner	silicone/acrylates and fluoro-silicone acrylate lenses
Contex	Non-Allergenic Clear Clean	silicone & fluorosilicone acrylates
Contex	Polish Brite/ Super Cleaner	silicone & fluorosilicone acrylates
Danker Labs	Perma-Brite	silicone & fluorosilicone acrylates
Lobob	Optimum by Lobob Extra Strength Cleaner	silicone & fluorosilicone acrylates
Menicon	Unique pH	silicone & fluorosilicone acrylates
Optikem International	Sereine Cleaner	silicone & fluorosilicone acrylates
Optikem International	Sereine Soaking & Cleaning	silicone/acryl copolymers
Orion Vision Group	Lens Fresh Extra Strength	silicone & fluorosilicone acrylates
Wal-Mart	Equate Sterile Contact Lens Cleaner	silicone & fluorosilicone acrylates

Periodic Enzymatic Cleaners

Manufacturer	Name	Lenses Approved
Bausch + Lomb	Boston One-Step Liquid Enzymatic Cleaner	silicone and fluorosilicone acrylates
Menicon	Progent GP Protein Remover	fluorosilicone acrylates

Daily Protein Removers

Manufacturer	Name	Lenses approved
Alcon Vision LLC	Opti-Free Supra-Cleas Daily Protein Remover	silicone acrylate and fluorosilicone acrylate lenses
Advanced Vision Technologies	Naturalens GP Cleaner	silicone acrylate and fluorosilicone acrylate lenses

Oxidation Systems

Manufacturer	Name	Lenses approved
Alcon Vision LLC	CLEAR CARE PLUS Cleaning & Disinfecting Soln.	3% hydrogen peroxide, .79% sodium chloride; contains catalytic disc for autoneutralization; with Hydralyde Moisture Matrix; requires digital rub for use with all GP lenses.
Alcon Vision LLC	CLEAR CARE Cleaning & Disinfecting Soln.	3% hydrogen peroxide, .79% sodium chloride; contains catalytic disc for autoneutralization; requires digital rub for use with all GP lenses.

Note: Previously listed AMO Products were purchased by Johnson & Johnson Surgical Vision, Inc.

Wetting and Lubrication

Manufacturer	Name	Lenses Approved
Advanced Vision Research	TheraTears Contact Lens Comfort Drops	silicone/acryl & fluorosilicone/acryl lenses
Alcon Vision LLC	Opti-Free RepleniSH Rewetting Drops	silicone/acryl & fluorosilicone/acryl lenses
Bausch + Lomb	Boston Rewetting Drops	silicone acrylate lenses and fluoro-silicone-acrylates
Danker Labs	Perma-Cote	silicone & fluorosilicone acrylates
Johnson & Johnson Surgical Vision, Inc.	Blink Contacts Lubricating Eye Drops	silicone/acryl & fluorosilicone/acryl lenses
Johnson & Johnson Surgical Vision, Inc.	Blink-N-Clean Lens Drops	silicone/acryl & fluorosilicone/acryl lenses
Lobob	Optimum by Lobob W/RW(wetting & rewetting)	silicone & fluorosilicone acrylates
Optikem International	Sereine Wetting	silicone acrylate lenses

Storage and Disinfection

Manufacturer	Name	Lenses Approved
Bausch + Lomb	Boston Advance Comfort Formula Conditioning Solution	silicone acrylates and fluoro-silicone acrylate lenses
Bausch + Lomb	Boston Conditioning Solution	silicone acrylates and fluoro-silicone acrylate lenses
Optikem International	Sereine Wetting & Soaking Solution	silicone & fluorosilicone acrylates

Combination Solutions

Manufacturer	Name	Lenses Approved
Bausch + Lomb	Boston Simplus Multi-Action Solution	silicone/acrylate and fluoro-silicone acrylate lenses (removing protein, cleaning/disinfecting/conditioning/cushioning)
Best Health, Inc.	Lens Comfort Multipurpose Solution	silicone/acrylate & fluoro-silicone acrylate lenses (cleaning, rinsing, conditioning, disinfecting); to be used with ultrasonic cleaning and disinfecting unit.
Lobob	Optimum by Lobob C/D/S	silicone & fluorosilicone acrylates (cleaning, disinfecting, soaking)
Menicon	Unique PH Multipurpose Solution	silicone & fluorosilicone acrylates (cleans, conditions, disinfects)
Tangible Science	Tangible Clean Soln.	silicone & fluorosilicone acrylates (cleans & disinfects)
Wal-Mart	EQUATE STERILE CL Conditioning Solution	silicone & fluorosilicone acrylates (wetting, disinfecting, soaking)

Saline for Scleral Lens Insertion

Manufacturer	Name	Lenses Approved
B + L Specialty Vision Products	ScleralFil	for insertion of scleral lenses; & rinsing of soft & GP lenses; 10 ml vials.
Menicon	LacriPure	sterile non-preserved saline for rinsing & insertion of scleral lenses; 5 ml vials.
Purilens/ Lifestyle Co. Inc.	Purilens Solution	preservative-free buffered saline in 4 oz. bottles